

#### **About ADM Cedar Rapids**

Archer Daniels Midland Company is one of the largest agricultural processors in the world producing food ingredients, animal feed ingredients, renewable fuels and naturally derived alternatives to industrial chemicals. Founded in 1902 and incorporated in 1923, ADM operates more than 250 processing and manufacturing facilities across the United States and worldwide. In 1971 ADM acquired Corn Sweeteners, Inc, Cedar Rapids, Iowa, forming ADM Corn Sweeteners, which contributed to the company's position as a world leader in corn sweeteners, dextrose, crystalline fructose, maltodextrin and other food and beverage ingredients. In 1981 the Cedar Rapids facility was expanded to produce ethanol.

#### **Customer challenge**

Managing pH in high-temperature chemical applications is critical for consistent product quality, efficient process reaction, and compliance in environmental regulations. But because accurate measurement requires immersing pH sensors in hot, strongly acidic substances for extended time periods, companies have traditionally had to replace them every few days. ADM Cedar Rapids, however, has found a pH sensor that they can use for months without replacing, thus significantly reducing equipment and labor costs, while maintaining high process quality standards. ADM has applied the new pH monitoring solution to provide



accurate, cost effective pH sensing to ethanol production at its Cedar Rapids, lowa facility.

Ethanol is a high-alcohol, renewable fuel additive that helps gasoline producers environmental regulations. Maintaining accurate pH levels during ethanol production is critical to control the sulfur dioxide levels. Excessive sulfur dioxide in the ethanol corrodes the carburetor and other engine components involved in gas distribution.

Ethanol production fermenting and distilling starch and sugar crops. In the early stages, liquefied starch is converted to sugar (dextrose), which is then fermented. Yeast is added to the mash to convert the sugars to ethanol and carbon dioxide. The fermented mash, called "beer," contains about 11 percent alcohol, as well as all the non-fermentable solids from the corn and the yeast cells. The beer is then heated to 235°F, to evaporate alcohol content, which is collected and condensed, and run through a rectifier to eliminate the remaining water. The final product is 199-proof, almost pure alcohol, ethanol.

"We tried taking pH readings directly from the process, but the 235° temperature ate sensors up," says Lloyd Feickert, instrumentation supervisor at the ADM Cedar Rapids facility. "To reduce excessive sensor costs we set up a slipstream arrangement, whereby we run a sample of the ethanol offline to cool it down to 140 degrees F., and measure that," says Feickert.

While the slipstream arrangement significantly extended pH sensor service life, inherent process conditions still caused frequent replacement of components in the rebuildable pH sensors. "At the lower temperatures, pH sensors could last for weeks, but process conditions caused temperature fluctuations within the slipstreams. These reduced sensor life significantly. We had standardized on the

Foxboro 871 rebuildable pH sensors, so we turned to them for the solution," says Feickert.

### **Foxboro Solution**

To accommodate ADM's application, the Foxboro Measurements & Instruments division of Invensys worked with Feickert to develop a field replaceable measuring electrode that could withstand severe temperature cycling up to 250°F. The replaceable electrode incorporates patented technology from the awardwinning Foxboro DolpHinTM pH sensor line.

"I heard about the DolpHin line of high temperature pH sensors and asked Foxboro if they could develop a similar product for rebuildable sensors. They studied my application and came back with a replaceable electrode that, after a cooperative testing period, increased our sensor service life from days to months," says Feickert.

The newly developed measuring electrode features a unique pH glass formulation that provides superior measurement stability, accuracy, and longer service in high-temperature applications. This pH glass also increases response speed up to five times. The electrodes are available in domed, spherical, or ruggedised flat glass. The domed glass electrode is for the harshest applications: temperatures up to 250°F and extremes of chemical concentrations.

The spherical glass electrodes are for standard process applications up to 212°F, and the flat ruggedised glass electrodes are for applications where the process water contains solid materials with pH between 2 and 12 and temperatures up to 185°F. All electrodes are interchangeable and their plug-in design facilitates quick and easy replacement to address changes in measurement conditions or application.

"Rebuildable sensors are definitely the most cost effective way to measure pH for our applications," says Feickert. We have standardized on the Foxboro 871 line and now, with the addition of the high temperature domed electrode, we have all the tools to cost effectively handle pH sensing throughout our plant."

#### Results

"The domed 871PH electrode has increased pH sensor service life from 10 days to four months," says Feickert. "That's a 1000 percent increase! When you consider that we use the domed sensor in four beer stills, as well as other processes within the plant, that's an enormous savings.'

In addition to the product cost savings, ADM has significantly reduced labor and maintenance costs. "Every time you send a person out to work on a sensor, it's at least an hour's worth of labor., I estimate that we have reduced time spent on changing electrodes over the course of a year from 36 hours per electrode to three hours per electrode," says Feickert.

# **AUTHOR DETAILS**

### John P. Connelly

Product Manager, Electro Chemical Measurement Devices Invensys Process Systems, Measurements

& Instruments Division 38 Neponset Avenue, Foxboro. MA 02035 - USA

Tel: + 1-508-549-4681 Fax: + 1-508-549-3684

# Email:

john.connelly@ips.invensys.com

www.foxboro.com/instrumentation

## Modern Spectrophotometer for Water and Waste Water Testing



The SpectroDirect is a modern single-beam spectrophotometer with an excellent price/performance ratio that is specifically designed for water testing.

The instrument is equipped with a wide range of pre-programmed methods based on the proven range of Lovibond® tube tests, tablet reagents, liquid reagents and powder reagents (Vario Powder Packs).

The light source is a tungsten halogen lamp with flash function. The lamp is switched on only momentarily during of the measurement process, so there is no need for a warm-up period. The SpectroDirect is ready to perform a self-test as soon as it is switched on.

The light passes through an entry slot to the monochromator, where it is split into spectral ranges. The monochromator is a holographically produced, transparent grating. The movable mirror ensures that light of the desired wavelength is focused automatically so that it passes through the exit slot, into the sample

chamber and therefore through the water sample. The light that is not absorbed by the sample travels to the silicon photodiode detector. This signal is then evaluated by a microprocessor and shown as a result in the display.

New methods, Test methods are continuously updated to suit market requirements. New methods can be added easily and quickly using software available from Tintometer (Germany).

Applications: Waste Water, Drinking Water, Industrial Process Water, Scientific & Research, Governmental and Private Laboratories, Advantages, Wavelength range from 330 to 900 nm, Interface RS232, Large illuminated graphic display, Touch-sensitive film keypad with logical layout, Use of round vials and rectangular cells of different sizes without adapter, 16 user-specific methods\*, Fast, easy lamp change, Software updates free of charge.

tyco / Flow **Environmental** | Control | Systems New PS2100 Level Logger

Welcome to a new level of accuracy and functionality!

- · Ceramic transducer
- · 36 Point Temperature Compensation
- · User definable engineering units
- · Modem ready for remote download
- Minimum logging frequency 0.2secs
- · 0.1% Full scale accuracy
- · Dual logging schedules for critical data capture
- · Detachable cable
- · 2Mb built-in Logger
- · 22mm diameter
- ·Internal Power



GREEN**span** www.tyco-environmental.com

UK Ph: +44 (0) 1256 817 800 email: cgibson@tyco-environmental.co.uk